

257-333



PROP80

P656T

DYNAMIC CARDIOID FLOATING

Floating output to allow a long cable run to an amplifier. The PROP80 has a sturdy base, a flexible gooseneck, lockable 'Talk' switch, "Busy" indicator lamp and extra switch contacts for priority page circuits. Ideal for use with all Eagle amplifiers and most others.

Sensitivity.....	0.4 mV at 94 dB spl
Impedance.....	600Ω
Response.....	200 to 12,000 Hz.
Cable.....	approx 3 metres
Switching	300 mA, low voltage