


Epson Stylus Office BX305F

PRODUCT GUIDE



This rugged business all-in-one gives your office laser-like printing, plus scanning, copying and faxing in one neat device. It also has an automatic document feeder to make light work of multi-page jobs.

Add efficiency and productivity to your business with this reliable 4-in-1. With 5 speed-dial fax buttons and an auto document feeder, it's faster and easier to fax, scan and copy multiple pages.

Print laser-like text documents, vibrant colour and brilliant graphics with Epson DURABrite Ultra Ink, and control, edit and share scanned documents easily with Presto! PageManager® 9 software.

WHAT'S IN THE BOX

- Epson Stylus Office BX305F
- 4 individual ink cartridges
- Software CD
- Basic operations guide
- 'Start Here' guide
- Control panel icon sticker
- Warranty document
- Power cable
- Phone cable
- Presto! PageManager® 9 Software

FOR THE BEST RESULTS ALWAYS USE GENUINE EPSON INK.

Epson DURABrite Ultra Ink is perfect for all your office printing because it gives you long-lasting Epson quality on a wide range of media.

- Laser-like text documents and vibrant colour
- Instant-drying prints are water, smudge, highlighter and fade resistant
- Resin-coated pigment technology works perfectly on a wide range of media



EPSON[®]
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

PRINT TECHNOLOGY	
Printing method	4-colour inkjet printer, Epson Micro Piezo™ print head
Nozzle configuration	90 nozzles black / 29 nozzles, each colour (cyan, magenta, yellow)
Droplet size	4 pl (minimum) with Variable-sized Droplet Technology
Ink system	Epson DURABrite Ultra Ink
PRINT RESOLUTION	
	Up to 5760x1440 optimised dpi on suitable media using RPM (Resolution Performance Management)
PRINT SPEED	
Black text A4	Up to 34 ppm*1
Colour text A4	Up to 15 ppm*1
Photo 10x15 cm	Approx. 72 secs*1
SCANNING	
Resolution	1200x2400 dpi
Technology	A4 flatbed colour image scanner
Sensor type	CIS
Speed	Black A4: 300 dpi 2.2 msec/line, 600 dpi 7.0 msec/line Colour A4: 300 dpi 7.5 msec/line, 600 dpi 13.1 msec/line
FAX FUNCTION	
Type of fax	Walk-up Black and white and colour fax capability
PC fax	Yes
Fax speed	Up to 33.6 kbps
Fax resolution	Standard (200x100), Fine (200x200), Photo (200x200 with error diffusion)
Error correction mode	CCITT/ITU Group3 fax with Error Correction Mode
Fax speed dials (max)	60 names and numbers
Page memory	Up to 180 pages (ITU-T No.1 chart)
Fax transmission speed	Approx. 3 sec per page
Other functions	Group dial, Delayed fax, Broadcast fax (mono only)
ADF FUNCTION	
Maximum document size	A4
Paper type	Plain paper only
Paper thickness	75-95 g/m ²
Maximum number of pages	30 (based on Xerox-P 75 g/m ²)
LCD SCREEN	
	2-line text
INTERFACE	
USB	Hi-Speed USB – Compatible with the USB 2.0 Specification*2
PAPER HANDLING	
Capacity	Input: 120 sheets A4 plain paper (64 g/m ²)
Media size	A4, Letter, Legal, 20x25 cm, 13x20 cm, 13x18 cm, 10x15 cm, 9x13 cm, A5, A6, B5, 16:9 wide size, Envelopes: No.10, DL, C6
Print margin	0 mm top, left, right, bottom via custom settings in printer driver*3
INK CARTRIDGES	
	4 individual ink cartridges
Apple series	Black Cyan Magenta Yellow T1291 T1292 T1293 T1294
Fox series	T1281 T1282 T1283 T1284
ELECTRICAL SPECIFICATION	
Power consumption	Approx. 10W (standalone copying, ISO/IEC24712 Pattern) Approx. 2.2W (sleep mode) ENERGY STAR® qualified all-in-one
Voltage	AC 220-240V
OPERATING SYSTEMS	
	Windows XP/XP-x64/Vista/7, Mac OS 10.4.11 or later
WARRANTY	
	1 year standard warranty Optional extension to 3 years subject to availability
GENERAL	
Dimensions (WxDxH)	460x411x235 mm
Weight	7.1 kg (excluding ink cartridges and power cable)
Noise level	5.3 B(A) (according to ISO7779 pattern with Epson Premium Gloss Photo Paper/Photo RPM mode) 38 dB(A) (according to ISO9296)
SOFTWARE	
	Epson Easy Photo Print, Fax Utility, Epson Web Support, Presto! PageManager® 9

*1 For more information please visit www.epson-europe.com

*2 USB cable required for PC/Mac use (not supplied in box).

*3 Otherwise 3 mm top, left, right, bottom.

Epson Stylus Office BX305F

INK CARTRIDGE COMPATIBILITY



- T1291
- T1292
- T1293
- T1294
- T1295



- T1281
- T1282
- T1283
- T1284
- T1285



Better Products for a Better Future

For more information please contact

Telephone: 0871 222 6702 (UK)*
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

* Calls cost 10 pence per minute from a standard BT landline.
Calls from other networks and mobiles may vary.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.