



REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	05/25/06	HO	05/25/06



NOTES:

- MOLDED CONNECTOR END REQUIREMENTS:
 - INNER MOLD USING PE
 - ALUMINUM FOIL WRAP TO CONNECTOR
 - PVC - 45P PLATINUM GRAY
- CABLE: [28AWG (7/0.12)*8C+AL/MY+DW(7/0.16)]TIN
 WIRE: OD=0.78±0.03mm
 COLOR: COLOR CODE
 JACKET: PVC, OD=5.0±0.15mm
 COLOR: PLATINUM GRAY
- THUMBSCREW: MALE 4*47mm NICKEL-PLATING
- CONNECTOR: DB9P FEMALE NICKEL-PLATING, INSULATOR COLOR: BLUE



SECTION A-A

PIN OUTS			
DB9P FEMALE		DB9P FEMALE	
4	BLACK	1	
1		6	
6	BROWN	4	
2	RED	3	
3	ORANGE	2	
5	YELLOW	5	
7	GREEN	8	
8	BLUE	7	
9	PURPLE	9	
Shell		Shell	

SPC TYPE No.	LENGTH
SPC19917	72±1 [1829±25.4]
SPC19916	120±2 [3048±50.8]

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
EKLAS ODISH	04/17/06
CHECKED BY:	DATE:
THOMAS LEE	05/25/06
APPROVED BY:	DATE:
HISHAM ODISH	05/25/06

DRAWING TITLE: Async Null Modem File Transfer Cable, DB9 F/F			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-733	TA-733.DWG	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	