


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	8/8/01	TJC
B	CORRECTED DIMENSIONS INDICATED	4/29/04	T CLARK
C	ECN#2024: REMOVING 4 SCREWS ON MALE SIDE	03/31/05	M.LAHEY
D	ECN 3322: UPDATE DWG FORMAT	5/13/08	D.GRIFFIN



**NOTES:**

MOUNTING FLANGE: NICKEL-PLATED STEEL  
CONNECTOR SHELLS: NICKEL-PLATED CAST ALUMINUM; INSULATOR MATERIAL PBT.  
CONTACT PLATING GOLD NICKEL FLASH ON COPPER ALLOY BASE.  
WIRED STRAIGHT THROUGH  
ADAPTER IS PACKAGED WITH TWO HEX STANDOFFS TAPPED M3.5 X 0.6.  
(FOR OPTIONAL USE)

**PACKAGING:**  
INDIVIDUALLY PACKAGE IN A POLYBAG

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2[51] / -0 >60 [1524] ≤120 [3048] = +4 / -0 >120 [3048] ≤300 [7620] = +6 / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS	DATE
	DRAWN BY TJC	8/1/01
	CHECKED BY RC	8/8/01
	APPROVED BY RC	8/8/01
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR	

SIZE	FSCM NO.	DWG. NO.	REV.
<b>B</b>	<b>43321</b>	<b>CIB24BA</b>	<b>D</b>

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY IEEE-488 GPIB	
PRODUCT DESCRIPTION IEEE-488 BULKHEAD ADAPTOR MALE-FEMALE		
SCALE: 1:1	CAD FILE: CIB24BA.SLDDRW	SHEET 1 OF 1