






SECT. A-A

SECT. B-B




SECT. C-C

NOTES

1. ACCEPTS TERM. # 5479PBT
2. MATES WITH 5483-NA & 5484-NA

|      |      |      |            |          |    |
|------|------|------|------------|----------|----|
| 35   | 38.1 | 39.9 | 39-01-0153 | 5480-15  | 15 |
| 32.5 | 35.6 | 37.4 | -0143      | -14      | 14 |
| 30   | 33.1 | 34.9 | -0133      | -13      | 13 |
| 27.5 | 30.6 | 32.4 | -0123      | -12      | 12 |
| 25   | 28.1 | 29.9 | -0113      | -11      | 11 |
| 22.5 | 25.6 | 27.4 | -0103      | -10      | 10 |
| 20   | 23.1 | 24.9 | -0093      | -09      | 9  |
| 17.5 | 20.6 | 22.4 | -0083      | -08      | 8  |
| 15   | 18.1 | 19.9 | -0073      | -07      | 7  |
| 12.5 | 15.6 | 17.4 | -0063      | -06      | 6  |
| 10   | 13.1 | 14.9 | -0053      | -05      | 5  |
| 7.5  | 10.6 | 12.4 | -0043      | -04      | 4  |
| 5    | 8.1  | 9.9  | -0033      | -03      | 3  |
| 2.5  | 5.6  | 7.4  | 39-01-0023 | 5480-02  | 2  |
| A    | B    | C    | EDP NO.    | ENG. NO. | 極数 |

|                           |        |                                        |            |                                   |        |
|---------------------------|--------|----------------------------------------|------------|-----------------------------------|--------|
| 材料 MATERIAL               |        | P.B.T. UL 94V-0 (15% GLASS REINFORCED) |            | MOLEX-JAPAN CO., LTD. 日本モレックス株式会社 |        |
| 仕上 FINISH                 |        | —                                      |            | EDP NO. 39-01-0**3                |        |
| 適用電線範囲 WIRE RANGE         |        | —                                      |            | ENG. NO. SD -5480-N               |        |
| 被覆外径 INS. RANGE           |        | —                                      |            | REV C                             |        |
| DRAWN BY Y. TAKENOUCHI    |        | CHK'D BY                               |            | TITLE 名称: 2.5 LOW PROFILE HOUSING |        |
| APP'D BY                  |        | DATE                                   |            | SCALE 5-1 10-1                    |        |
| 角度 ANGLE                  | ± 3°   | C                                      | RELEASED   | ECN 3595                          | 9/1/83 |
| 30 以上 OVER                | ± 0.3  | B                                      | CHANGED BY | ECN 3387                          | 9/1/83 |
| 10 以上 30 未満 OVER 30 UNDER | ± 0.25 | A                                      | CHANGED    |                                   |        |
| 10 未満 UNDER               | ± 0.2  | O                                      | PROPOSED   |                                   |        |
| 一般公差 GENERAL TOLERANCES   | 記号 LTR | 変更内容 REVISION RECORD                   | DR. CHK.   | 日付 DATE                           |        |



|      |      |      |            |          |    |
|------|------|------|------------|----------|----|
| 35   | 33.1 | 34.9 | 39-01-0153 | 5480-15  | 15 |
| 32.5 | 35.6 | 37.4 | -0143      | -14      | 14 |
| 30   | 33.1 | 34.9 | -0133      | -13      | 13 |
| 27.5 | 30.6 | 32.4 | -0123      | -12      | 12 |
| 25   | 28.1 | 29.9 | -0113      | -11      | 11 |
| 22.5 | 25.6 | 27.4 | -0103      | -10      | 10 |
| 20   | 23.1 | 24.9 | -0093      | -09      | 9  |
| 17.5 | 20.6 | 22.4 | -0083      | -08      | 8  |
| 15   | 18.1 | 19.9 | -0073      | -07      | 7  |
| 12.5 | 15.6 | 17.4 | -0063      | -06      | 6  |
| 10   | 13.1 | 14.9 | -0053      | -05      | 5  |
| 7.5  | 10.6 | 12.4 | -0043      | -04      | 4  |
| 5    | 8.1  | 9.9  | -0033      | -03      | 3  |
| 2.5  | 5.6  | 7.4  | 39-01-0023 | 5480-02  | 2  |
| A    | B    | C    | EDP NO.    | ENG. NO. | 極數 |

注記

1. 適用ターミナル --- 5479PBT  
2. 嵌合相手 ----- 5483-NA  
5484-NA

|                              |  |           |                         |                           |                    |                                                 |  |                                         |  |
|------------------------------|--|-----------|-------------------------|---------------------------|--------------------|-------------------------------------------------|--|-----------------------------------------|--|
|                              |  |           |                         |                           |                    | 材 料<br>MATERIAL<br>P.B.T. UL94V-0<br>(15%ガラス入り) |  | MOLEX-JAPAN CO., LTD.<br>日本モレックス株式会社    |  |
|                              |  |           |                         |                           |                    | 仕 上<br>FINISH                                   |  | EDP NO.<br>39-01-0**3                   |  |
| 角度 ANGLE                     |  | ± 3'      | C                       | RELEASED ECH NO. 2595     | 2-1/4-54           | 適用電線範囲<br>WIRE RANGE                            |  | ENG. NO.<br>SD -5480-N                  |  |
| 30 以上<br>OVER                |  | ±0.3      | B                       | CHANGED BY<br>E.M.D. 3387 | 2-1/4-54           | 被覆外径<br>INS. RANGE                              |  | REV<br>C                                |  |
| 10 以上<br>OVER 30 未満<br>UNDER |  | ±0.25     | A                       | CHANGED                   | C.I. 11/4<br>237   | DRAWN BY 12/24/80<br>Y. TAKENOUCHI              |  | TITLE 名称:<br>2.5 LOW<br>PROFILE HOUSING |  |
| 10 未満<br>UNDER               |  | ±0.2      | O                       | PROPOSED                  | DATE               | CHK'D BY 11/5/83<br>Substima                    |  |                                         |  |
| 一般公差<br>GENERAL TOLERANCES   |  | 記号<br>LTR | 変更内容<br>REVISION RECORD |                           | DR. 日付<br>CHK DATE | APP'D BY                                        |  | 尺 度<br>SCALE 10-7                       |  |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX JAPAN) AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION  
本図面は日本モレックス㈱の所有する情報を含むもので当社の許可なく複製を禁止する。 MXJ-8

