







基板取付穴推奨寸法
RECOMMENDED P.C.B.HOLE DIMENSIONS



D	C	B	A	オーダー番号 ORDER NO.	極数 CIRCUIT
2.5	7.4	5.6	2.5	53052-0210	2
5	9.9	8.1	5	-0310	3
7.5	12.4	10.6	7.5	-0410	4
10	14.9	13.1	10	-0510	5
12.5	17.4	15.6	12.5	-0610	6
15	19.9	18.1	15	-0710	7
20	24.9	23.1	20	-0910	9
25	29.9	28.1	25	-1110	11
27.5	32.4	30.6	27.5	-1210	12
30	34.9	33.1	30	-1310	13
32.5	37.4	35.6	32.5	-1410	14
35	39.9	38.1	35	-1510	15
37.5	42.4	40.6	37.5	-1610	16
40	44.9	43.1	40	-1710	17
42.5	47.4	45.6	42.5	-1810	18
45	49.9	48.1	45	-1910	19
47.5	52.4	50.6	47.5	53052-2010	20

CONNECTOR SERIES NO. 53052-**10

注記
NOTES
1. 嵌合相手 : 51024-**00
MATES WITH : 51024-**00
2 キンクは両端のソルダーテールのみとする。
KINK TO BE APPLIED FOR THE BOTH END OF TERMINAL

RELEASED
EC NO: J2010-0316
DRWN:NNISHI 2009/08/31
CH'KD:NMATSUURA 2009/08/31
APPR:KMORIKAWA 2009/08/31
DESCRIPTION
REV 0

GENERAL TOLERANCES (UNLESS SPECIFIED)

10 UNDER	±0.3
10 OVER 30 UNDER	±0.25
30 OVER	±0.2
ANGULAR	±3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM ONLY
SCALE: 5:1
DESIGN UNITS: METRIC
THIRD ANGLE PROJECTION

DRAWN BY: NNISHI DATE: 2009/08/25
CHECKED BY: NMATSUURA DATE: 2009/08/25
APPROVED BY: KMORIKAWA DATE: 2009/08/25
MATERIAL NO.: SEE CHART

TITLE: 2.5 LOW PROFILE WAFER ASSY WITH KINK
MOLEX INCORPORATED
DOCUMENT NO.: SD-53052-001
SHEET NO.: 1 OF 1
SIZE: A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION