




RELEASED EC NO.: JTR2010-0090 DRWN: SANDO 2006/05/25 CHKD: MA. YAMAMOTO 2006/5/25 APPR: MAYAMOTO 2010/03/10	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY	SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
	10 UNDER	± 0.2	DRAWN BY S. ANDO	DATE 2006/5/25	TITLE CMC HEADER 80PIN		
	10 OVER 30 UNDER	± 0.25	CHECKED BY MA. YAMAMOTO	DATE 2006/5/25	MOLEX INCORPORATED		
	30 OVER	± 0.3	APPROVED BY MAYAMOTO	DATE 2010/03/09	MATERIAL NO. 502225-0801		
	ANGULAR ±2 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOCUMENT NO. SD-502225-001		SHEET NO. 1 OF 2		




基板穴推奨寸法 (部品実装側)
RECOMMENDED PCB LAYOUT (COMPONENT SIDE)



SECTION B-B
Scale 2:1

注記
NOTES

- ハウジング材料: PBT-GF30%, 黒色
HOUSING MATERIAL: PBT, GF30%, BLACK
- 端子材料: 銅合金
CONTACT MATERIAL: COPPER ALLOY
- 端子表面処理:
コンタクト部: 銅めっき
テール部: 銅めっき
接地コネクタめっき (025, 060端子全面)
CONTACT PLATING:
CONTACT AREA: Sn PLATING
TAIL AREA: Sn PLATING
UNDER NICKEL PLATING (ALL OVER)
- 適合基板厚: 1.6±0.1mm
APPLICABLE PCB THICKNESS: 1.6±0.1mm
- 適合適合コネクタ:
64319-3211 (32ピン, 黒, 右)
64320-1519 (48ピン, 茶, 左) 又は,
64319-1211 (32ピン, 黒, 左)
64320-3319 (48ピン, 茶, 右)
APPLICABLE MATING CONNECTOR:
64319-3211 (32PIN, BLACK, RIGHT),
64320-1519 (48PIN, BROWN, LEFT) OR,
64319-1211 (32PIN, BLACK, LEFT),
64320-3319 (48PIN, BROWN, RIGHT)
- 製品仕様書:
PS-64319-001参照
PRODUCT SPECIFICATION:
REFER TO PS-64319-001



RELEASED EC NO: JTR2010-0090 DRWN: SANDO 2006/05/25 CHKD: MA.YAMAMOTO 2006/5/25 APPR: MAYAMAMOTO 2010/03/10	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
	10 UNDER	± 0.2	DRAWN BY S. ANDO	DATE 2006/5/25	TITLE CMC HEADER 80PIN				
	10 OVER 30 UNDER	± 0.25	CHECKED BY MA. YAMAMOTO	DATE 2006/5/25	MOLEX INCORPORATED DOCUMENT NO. SD-502225-001 SHEET NO. 2 OF 2				
	30 OVER	± 0.3	APPROVED BY MAYAMAMOTO	DATE 2010/03/09					
0	ANGULAR ±2 °	MATERIAL NO. SEE SHEET No.1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								