

C1

Har-flex 12P female connector

C2



Har-flex 12P female connector

Part-No./产品号码	Length/长度
33 15 243 050 0006 .00	500±5
33 15 243 020 0005 .00	200±3
33 15 243 010 0004 .00	100±3

NOTES/要求:

- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.
- 2.) CABLE OPERATION TEMPERATURE=-30° C TO +105° C .
- 3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION
HARTING P/N & REVISION

 All Dimensions in mm Original Size DIN A4		Ref. MB												
Free size tol.		Mat.												
V=	cm ³ A=	SEE BILL OF MATERIAL												
<table border="1"> <thead> <tr> <th>Name</th> <th>Date</th> <th>Scale</th> </tr> </thead> <tbody> <tr> <td>Detail</td> <td></td> <td>✓</td> </tr> <tr> <td>Insp.</td> <td></td> <td>Sheet</td> </tr> <tr> <td>Approved</td> <td></td> <td>1 of 1</td> </tr> </tbody> </table>		Name	Date	Scale	Detail		✓	Insp.		Sheet	Approved		1 of 1	Title
Name	Date	Scale												
Detail		✓												
Insp.		Sheet												
Approved		1 of 1												
ZHUHAI HARTING LIMITED 		Har-Flex female 12pole, double ended Flat cable assembly, L=xM												
DWG. No. TB_33 15 0002 .00														

00	Prototype	Andrew.H	24/05/11
Rev.	Description	Appr.	Date