

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

1

PARTS PACKAGED UNASSEMBLED.

2

CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY REVERSING CLAMPING INSERTS.
(2 INSERTS SUPPLIED, -1 AND -2 ONLY)

3

CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -4 ONLY)

4

.703 MAXIMUM CABLE OUTSIDE DIAMETER.

5

BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 100 ONLY.

6

NON-HEXAVALENT CHROMATE FINISH.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1.131±.025 DIA

1.655±.030

CLAMPING INSERT

(2) #5-20 SELF-TAPPING SCREWS, SOLID OR SLOTTED SHANK.
MATERIAL: ZINC PLATED STEEL
LENGTH: .62±.00 EXCEPT -6, .50±.05

CLAMPING AREA SHADED

CLAMPING INSERT

(2) #5-20 SELF-TAPPING SCREWS, SOLID OR SLOTTED SHANK.
MATERIAL: ZINC PLATED STEEL
LENGTH: .62±.00 EXCEPT -6, .50±.05

CLAMPING AREA SHADED

6	INDIVIDUAL	1-206322-1
6	5 BULK	1-206322-0
6	INDIVIDUAL	206322-9
6	7 OBSOLETE	SMALL PACK 206322-8
6	7 OBSOLETE	INDIVIDUAL 206322-7
6	5 BULK	206322-6
7	6 OBSOLETE	SMALL PACK 206322-5
	OBSOLETE	INDIVIDUAL 206322-4
6	SUPERSEDED BY 1-206322-0	5 BULK 206322-2
6	SUPERSEDED BY 206322-9	INDIVIDUAL 206322-1
PACKAGING		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A GRAFF 4/23/91	STE TE Connectivity CABLE CLAMP KIT, LARGE, SHELL SIZE 17, CPC		
DIMENSIONS: INCHES		CHK W.G.LENKER 7-22-92			
		APVD -			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-10024			
MATERIAL THERMOPLASTIC		FINISH -	APPLICATION SPEC -	WEIGHT -	NAME
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	SIZE A3	CAGE CODE 00779	DRAWING NO C-206322
			CUSTOMER DRAWING		RESTRICTED TO -
			SCALE NTS	SHEET 1 OF 1	REV P3

1470-19 (3/11)