

BODY



MATERIAL:
Body : Glass filled polyester
Ring : CuZn Alloy Ni plated
Elastomer link : Elastomer

NOTES :
-Operating temperature : -40° up to +105°
-This cap is a water and dust protected version.
-Level sealing : IP68 (1bar during 1 week)

PART NUMBER	∅A	B max
UTS610DCG	19.5	136 max.
UTS612DCG	23.5	140 max.
UTS614DCG	27	143 max.
UTS618DCG	33	150 max.



CUSTOMER DRAWING

C	21/06/2013	-- Modification of sealing Level	22980
ISS	DATE	Latest modification - by: BERTHOME A.	MOD N°

Designed by: SORIN V. Date: 07/04/06 — Type of drawing: Customer

Checked by: SEE DISTRIBUTION LIST — Date: SEE DISTRIBUTION LIST

TITLE: UTS PLUG SEALING CAP --

Scale 2/1 — General angular Tolerances: ± -- — MATERIAL —

General linear Tolerances : ±0.2 — General machining surface texture Ra 3.2 — Geometrical Tolerances See NF E 04-552 — PROJECT UTS1

SOURIAU
Route Nationale 23
72470 CHAMPAGNE
Tel. (33)02.43.54.35.00

This document is the property of SOURIAU
It must not be reproduced or communicated without permission

FORMAT A3 — SOURIAU DRG N° C004-UTS1-A — SHEET 1 /1