


SUPPLIED TAPED + REELED 100X PER REEL



CIRCUIT

SPECIFICATION (WITH APPROVED PLUG)
 RATED: 10A / 20V 4.3uF
 INSERTION FORCE: 2.5Kg max
 WITHDRAWAL FORCE: 1.0Kg~2.5Kg
 INSULATION RESISTANCE: >500MΩ@500VDC
 WITHSTAND VOLTAGE: 250VAC/1 MIN
 CONTACT RESISTANCE: <7mΩ

ROHS
COMPLIANT

TOLERANCE
 NO DEC. PLACE ±0.30
 1 DEC. PLACE ±0.20
 2 DEC. PLACE ±0.10
 HOLE Ø ±0.10
 ANGLES ±1/2°
 UNLESS OTHERWISE STATED

DO NOT SCALE

Cliff Electronic Components Ltd.

76 Holmechurpe Avenue, Holmechurpe Industrial Estate,
 Redhill, Surrey, RH1 2PF, England, UK
 Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
 TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2007

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK	
MATERIAL:	PPO / BRASS / SS / COPPER
FINISH:	AS MOULDED / Sn / Ag PLATED
DRAWN:	C.A.M.J.
APPROVED:	R.W.T.
PACKED ON TAPE / REEL	

TITLE:	DC POWER SOCKET Ø2.5mm
DRWG. No.	FC681495
FORM:	ADDRWGH

ISS.	AMEND	DATE
1	1st DRAWN	21/12/07
2	SPECN/PACKING ADD	15/01/07
3	Ø2.1 VARIANT DEL	21/11/12