

1

2

3

4

5

6

7

8

REV ZONE

ECO

DESCRIPTION

DATE

BY

APPR

A1

--

RELEASE NUMBER

02/09/12

--

--

A2

--

C0081S

03/02/13

JARRY

--

1

2

3

4

5

6

7

8

1. 材料 Material.
绝缘体:热缩性塑料,UL 94V-0;
Insert: thermoplastic,UL 94V-0;
颜色:ATP04-2P=灰色,ATP04-2P-BLK=黑色
Color:ATP04-2P=Gray,ATP04-2P-BLK=Black

2. 工作温度 Operation temperature: 55° C ~+125° C;

3. 性能参数 Specification:
3.1 额定电压 Rating Voltage: 250VAC MAX;
3.2 额定电流 Rating current: 25A;
3.3 耐受电压 Withstanding voltage: 1500VAC;
3.4 绝缘电阻 Insulation resistance: 1000MΩ;
3.5 接触电阻 Contact resistance: 10mΩ;
3.6 防水等级 Waterproof: IP67;
3.7 机械寿命 Mating cycles: 100 cycles;

4. 互配产品:ATP06-2S-XXXX (XXXX=所有扩展料号);
Mating part:ATP06-2S-XXXX (XXXX=A11 Extended Part);

5. 与产品互配的端子和线缆规格 Mating contacts and wire.

Amphenol PCD Shenzhen

受控文件

2013年2月25日

21.6

47.0

18.6

22.0

AMPHENOL
ATP04-2P

AMPHENOL

2

Ø2.6

AMPHENOL
ATP04-2P

ITEM

PART NUMBER

Qty

DESCRIPTION

REMARK

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED:
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30
2 PL DEC ±0.15
3 PL DEC ±0.08

签 名 SIGNATURE

日期 DATE

03/02/13

制 图 DRAWN

审 核 CHECKED

工 艺 ENGINEER

批 准 APPROVAL

客 户 CUSTOMER

JARRY

Orion Li

Tangyiwie

2013.02.22

-21:39:39+09:00

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF AMPHENOL CORPORATION. NO RIGHTS OF INVENTION ARE RESERVED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

SINE Systems Corporation

A Subsidiary of Amphenol Corporation

Assembly Connector Receptacle, 2 way

DWG NO: ATP04-2P-XXX

第三角投影
THIRD ANGLE
PROJECTION

文件编号
FILE NO.

幅 面
SIZE

质 量
MASS

版 次
REV.

比 例
SCALE

1 OF 1

NEXT ASSY:

A

B

C

D

E

F