

D

C

B

A

D


C

B

A

AMP AND PART NO
THIS SURFACE


.443
.319
.212
.105
.000
.019
.143
.250
.357
.464



MATING FACE

(-1 ONLY)

AMP AND PART NO
THIS SURFACE



MATING FACE

(-2 ONLY)

- CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
- WILL ACCEPT (57) SIZE 20 PIN CONTACTS.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

COUPLING RING
POLYESTER, BLACK

PLUG HOUSING
NYLON 6/6,
GLASS FILLED,
BLACK

1.783 MAX DIA

.915 MAX

COUPLING RING
POLYPHENYLENE,
BLACK

PLUG HOUSING
NYLON 6/6,
GLASS FILLED,
BLACK

1.738 MAX DIA

.915
MAX

	OBSOLETE	206437-2
		206437-1
	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.STAUB BG 4/2/91	TE Connectivity			
		CHK W.G.LENKER 7-23-92				
		APVD K.BEAVER 7-23-92	NAME			
		PRODUCT SPEC 108-10024	PLUG ASSEMBLY, REV SEX, SERIES 2, 23-57, CPC			
		APPLICATION SPEC				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	SIZE A2	CAGE CODE 00779	DRAWING NO C-206437	RESTRICTED TO -
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH -	WEIGHT -	SCALE 2:1	SHEET 1 OF 1	REV G2
MATERIAL SEE CALLOUT		CUSTOMER DRAWING				