

PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL  
 INSULATOR MATERIAL: PBT  
 FLAMMABILITY RATING: UL94-V0  
 COLOR: BLACK  
 CONTACT MATERIAL: COPPER ALLOY  
 CONTACT TYPE: STAMPED  
 CONTACT PLATING: SELECTIVE GOLD  
 SHIELDING: BRONZE NI PLATED  
 QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL  
 OPERATING TEMPERATURE: -25 °C UP TO 85 °C  
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL  
 CURRENT RATING: 1.5 A  
 WORKING VOLTAGE: 120 VAC  
 INSULATION RESISTANCE: >500 MΩ  
 DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN  
 CONTACT RESISTANCE: 20 mΩ MAX

STANDARD  
 CERTIFIED: E324776

SOLDERING  
 JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING  
 TRAY

RoHS Compliant


G			
F			
E	17-JUL-14	CHARACTERISTICS	AS
D	03-JAN-14	TPK DWG ADD	QL
C	24-NOV-09	PINNING & DIM.	JP
B	07-OCT-09	UL STANDARD	JP
A	12-SEP-07	PDF	CH
REV	DATE	FILE	BY

PROJECTION:	
APPROVAL: RJ	



GENERAL TOLERANCE
.X = +/- 0.2
.XX = +/- 0.15
UNIT: MM
SCALE:
SHEET: 1/1
DRAW:



DESCRIPTION: HORIZONTAL PLASTIC 6P6C MODULAR JACK TAB DOWN	SIZE <b>A4</b>
WERI PART NO: 615 006 143 621	



Packaging Qty		
168 pcs/Tray	18Trays/Carton	3024 pcs/carton

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	
G						
F						
E						
D				APPROVAL: RJ	UNIT: MM	DESCRIPTION: HORIZONTAL PLASTIC 6P6C MODULAR JACK TAB DOWN  WERI PART NO: 615 006 143 621
C					SCALE:	
B					SHEET: 1/1	
A					DRAW:	
REV	DATE	FILE	BY			SIZE <b>A4</b>