




10° TYP.

MATING FACE

RAISED CAVITY IDENTIFICATION

3,0 DIA. TYP.

26

18

9

10

19

2,5R.TYP.

33,3

39,1

7,9

NOTES:

1

THIS RECEPTACLE ACCEPTS SIZE 22 REC. CONTACTS.

2

RETENTION TINES ARE AN INTEGRAL PART OF INSERT.

3

CONTACT INSERTION/REMOVAL TOOL TE P.N. 91285-1 IS RECOMMENDED FOR USE WITH THESE CONNECTORS:

FRONT SHELL
STEEL,BRIGHT TINPLATED.

REAR SHELL,STEEL
BRIGHT TINPLATED.

TE DATE CODE
TE PARTNO.
INK STAMPED

0,8

10,9 MAX.

24,7

27,5

6,2

10,9

10,7

12,5

INSERTS:NYLON
GLASS-FILLED
SELF-EXTINGUISHING
COLOR: BLACK

CLINCH
SECTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

WIRE RANGE

INSUL.RANGE

DWN
J.V.D.HEIJDEN.

CHK
C.v.TILBURG.

APVD
L.v.SOEST.

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

07-12-88

02-01-89

04-01-89

—

—

—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
B

SEE DRAWING

FINISH

SEE DRAWING

MATERIAL

216165-1

PARTNUMBER

TE Connectivity

NAME

HDP-22 REC. CONNECTOR,
SIZE 2, (26 POSITION)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-216165

—