




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT -

ALL RIGHTS RESERVED.


REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.



SCALE 3:1



SOLDER DETAIL
SCALE 10:1




NOTES:


- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S3	APPLICATION SPECIFICATION NUMBER ADDED	24JUL2013	KJK	RP

1 PARTNUMBER VAC. TAPE.	3 PARTNUMBER	NR.OF POS. "n"	"A"	"B" MAX.
7-188275-4	0-188275-4	4	3,81	7,1
7-188275-6	0-188275-6	6	6,35	9,7
7-188275-8	0-188275-8	8	8,89	12,2
8-188275-0	1-188275-0	10	11,43	14,7
8-188275-2	1-188275-2	12	13,97	17,3
8-188275-4	1-188275-4	14	16,51	19,8
8-188275-6	1-188275-6	16	19,05	22,4
8-188275-8	1-188275-8	18	21,59	24,9
9-188275-0	2-188275-0	20	24,13	27,5




ACCORDING EIA-481/DIN IEC 286



POLARIZATION-SLOT
ON THIS SIDE.

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR



RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.GOSSELINK	 TE Connectivity	
DIMENSIONS: mm		CHK -		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		
0 PLC ±-		PRODUCT SPEC 108-19052		
1 PLC ±-		APPLICATION SPEC 114-13318	NAME CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MaTch	
2 PLC ±-		WEIGHT -	SIZE A3	CAGE CODE 00779
3 PLC ±-		DRAWING NO C-188275		RESTRICTED TO -
4 PLC ±-		SCALE 5:1		SHEET 1
ANGLES ±-		OF 2		REV S3
FINISH SEE TABLE		CUSTOMER DRAWING		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION


DATE

DWN


APVD

SEE SHEET 1


TAPE WIDTH 24 mm




7-188275-4 7-188275-6 7-188275-8 8-188275-0
4 POSITION 6 POSITION 8 POSITION 10 POSITION
0-188275-4 0-188275-6 0-188275-8 1-188275-0



TAPE WIDTH 44 mm




8-188275-2 8-188275-4 8-188275-6 8-188275-8 9-188275-0
12 POSITION 14 POSITION 16 POSITION 18 POSITION 20 POSITION
1-188275-2 1-188275-4 1-188275-6 1-188275-8 2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.1
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±.
4 PLC ±.
ANGLES ±.
FINISH

DWN

M. GOSSELINK

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-188275

SCALE

1:1

SHEET

2

OF

2

REV

S3