


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
G	14		L	REV PER ECR 10-000722	25JAN10	JR
						APVD
						TM



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1

STAMP AMP 2/0W* APPROX AS SHOWN
- 2

COPPER PER ASTM B-152, ANNEALED
- 3

TIN PLATE 0.00254 [0.000100] MIN THK
EXT. PER ASTM B-545
- 4 MAX RECOMMENDED OPERATING TEMP
IS 170°C.
- 5 WIRE CROSS SECTIONAL AREA RANGE:
60.6-76.3mm [119,500-150,500] CMA
SOLID OR STRANDED.

25	SMALL PACK	8-36925-3
50	LOOSE PIECE	36925
QTY	PACKAGING TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: MM [INCHES]		CHK AJ KAUFMAN 1/19/94				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 1/19/94	NAME TERMINAL, RING TONGUE, SOLISTRAND		
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -			
	FINISH		APPLICATION SPEC -			
MATERIAL		2	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-36925
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV L	RESTRICTED TO -