

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			H3	REVISED PER ECO-11-004820	11MAR11	RK

AMP
WIRE RANGE

4 AWG
SOLID OR STRANDED

- 1
- STAMP AMP 4W* APPROX AS SHOWN

2


3

4

5



6

7



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 16.8-26.7mm²[33,100-52,600] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

67	20	LOOSE PIECE, BOX	4	8-34320-5
---	----	LOOSE PIECE	5	34320-1
67	----	LOOSE PIECE	4	34320
APPROVALS	QTY	PACKAGE TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-14-93	 TE Connectivity					
DIMENSIONS: INCHES		CHK DA PATTERSON 4-14-93						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD DA PATTERSON 4-14-93	NAME SPLICE, PARALLEL, SOLISTRAND					
		PRODUCT SPEC —						
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —		
		MATERIAL - 	FINISH SEE TABLE	WEIGHT —	A2		00779	C=34320
CUSTOMER DRAWING			SCALE	10:1	SHEET	1 of 1	REV	H3