


LOC		DIST		REV		REVISIONS		DATE		APPRO	
6	14	P	F	ZONE	LTR	DESCRIPTION		DATE		APPRO	
				B	REV, RDRW, & SM PKG	PER 0720-0040-93		2-24-93		18 DAP	

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
26-22 AWG SOLID OR STRANDED	NOT LISTED
 LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

1 STAMP AMP APPROX AS SHOWN
2 MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.1-0.41mm² [202-810] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ± ANGLES ±	DR 2-24-93 TA BRINKMAN CHK 2-24-93 DA PATTERSON APPD 2-24-93 DE MILLER APPD 2-24-93 JL MECKLEY PRODUCT SPEC APPLICATION SPEC WEIGHT - SCALE 10:1	NAME AMP AMP Incorporated Harrisburg, PA 17105-3608
100	LOOSE PIECE, BOX	8-321198-1
----	LOOSE PIECE	321198
QUANTITY	PACKAGE TYPE	PART NO
SPlice, BUTT, STRAP, SOLISTRAND™		
SIZE	CAGE CODE	DRAWING NO
③	00779	③=321198
SHEET		1 OF 1