

10

9

8

7

6

5



4

3

2


1

引き出し方向
PULL OUT
DIRECTION




DETAIL "F"

引き出し方向
PULL OUT
DIRECTION




NOTES

- 製品詳細寸法については図面 SD-53729-004 を参照下さい。
RE DETAILED DIMENSION, SEE SD-53729-004
- 梱包数量：3000個/リール
NUMBER OF CONNECTORS : 3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(剥離方向は下図参照)

尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.



- 材料(MATERIAL)
キャリアテープ(CARRIER TAPE): ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE): PET, PE, PEF
リール(REEL): ポリスチレン(P.S) <リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>

REVISED	EC NO: J2015-0630	2014/11/10	DRWN: YSATO06	CHKD: TASAKAWA	2014/11/11	APPR: KMORIKAWA	2014/11/11	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
									10 UNDER	± ---	T. NIITSU	DATE '96/11/10	TITLE 0.5 BTB PLUG HGT=2 W/O BOSS EMBSTP PKG			
									10 OVER 30 UNDER	± ---	CHECKED BY T. ITO	DATE '01/2/21				
									30 OVER	± ---	APPROVED BY M. FUKUSHIMA	DATE '01/2/21	molex			
									ANGULAR ± --- °		MATERIAL NO.					
D	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-53729-002		1 OF 2								
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														

