

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior concert, & that no right is granted to disclose or to use any information in this document.


Customer drawing

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	09/01/08	IP
2	HK--	Update the Drawing	11/28/13	IP







Cover



With Insulator Support





Strain Relief

D-SUB TECHNICAL DATA

BODY : Glass-Filled Thermoplastic PBT, UL94V-0

CONTACTS : Copper alloy
Gold flash over 50u'' nickel on mating area
100u'' tin over 50u'' nickel on solder area

ELECTRICAL : Voltage rating 250 VAC/Rms 60Hz
Current Rating :3 AMP
Withstanding Voltage >1000 VAC Rms
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max

PRODUCT CODE

L 17D X FR B XX S

- L: RoHS Compliance
- 17D: Flash gold contact plating
- Shell Size:E,A,B,C
- Flat ribbon cable type
- Type: B=All plastic
- Configuration: 09,15,25,37
- Contact type: S=Socket

Dimensions

Positions	A	B	C	E	F
9	30.81	24.99	16.33	11.08	10.16
15	39.20	33.30	24.70	19.39	17.78
25	53.05	47.04	38.40	33.24	30.48
37	69.40	63.50	54.80	49.86	45.72

UNLESS OTHERWISE SPECIFIED
TOLERANCES
U.S. METRIC
.X +/- 0.50
.XX +/- 0.30
.XXX +/- 0.20
FRACTIONS +/-
ANGLES +/- 5°
FOR MATERIALS AND FINISHES SEE NOTES
REMOVE SHARP EDGES
DIMENSIONS
U.S. INCHES
METRIC MM

APPROVAL		DATE
DRAWN	Felix.Liu	11/28/13
CHECKED	Tony.Tang	11/28/13
CHECKED		

DRAWING FILE :

ANGLE OF PROJECTION

Amphenol
Amphenol East Asia Limited

TITLE
IDC flat cable D-SUB series

SIZE	DRAWING NO.	REV.
A4	C L17DXFRBXXS	2

SCALE NONE SHEET 1 OF 1