

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



(C) COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC
HDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	EHC0-0098-04	19-APR-04	PW	PJ
	B	ECR-09-003544	16FEB2009	PW	DH

SECTION A-A
SCALE 15:1DATE CODE:
DDYS

DATE CODE



SECTION B-B

NOTES:

- MATERIAL: HOUSING: GLASSFILLED LCP
CONTACT: BeCu
BRACKET: BeCu
- PLATING: UNDERLAYER 1.3 μ m NICKEL
0,5 μ m MIN. GOLD IN CONTACT ZONE
FLASH GOLD (0,2 μ m MAX.) ON SOLDER TAB
- CONTACT FORCE: 0,2N MIN. AT 1,1mm
0,6N MAX. AT 0,7mm
- INJECTION POINT 0,1mm RECESSED
- AREA FREE OF MARKING, SCRATCHES OR MOLDING DEFECTS
- PACKAGING: POCKETTAPE ACCORDING EIA 481-B
- NO BURRS OR CRACKS ON TOP OR SIDE OF DIMPLE SURFACE

PN. 1705536-2 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC $\pm 0,5$ 1 PLC $\pm 0,2$ 2 PLC $\pm 0,1$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$
MATERIAL	FINISH

DWN	P. WILLEMS	19-04-04
CHK	P. JAEGER	19-04-04
APVD	P. JAEGER	19-04-04
PRODUCT SPEC	108-19269	
APPLICATION SPEC		
WEIGHT		
CUSTOMER DRAWING		

TYCO ELECTRONICS NEDERLAND B.V.
's-HERTOGENBOSCH, THE NETHERLANDS


NAME	10 Pos Compressive Connector
SIZE	A3
CAGE CODE	00779
DRAWING NO	C=1705536
RESTRICTED TO	
SCALE	6:1
SHEET	1
OF	3
REV	B

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION -

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-						
			-	SEE SHEET 1	-	-	-



NOTES:
⚠ WITHIN THIS AREA NO UN-ISOLATED TRACKS PERMITTED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN P. WILLEMS 19-04-04	TYCO ELECTRONICS NEDERLAND B.V. 's-HERTOGENBOSCH, THE NETHERLANDS	
DIMENSIONS: mm		CHK P. JAEGER 19-04-04		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. JAEGER 19-04-04	NAME - 10 Pos Compressive Connector -	
0 PLC ±0,5 1 PLC ±0,2 2 PLC ±0,1 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-19269		
MATERIAL -		APPLICATION SPEC -	SIZE A3	
FINISH -		WEIGHT -	CAGE CODE 00779	
		CUSTOMER DRAWING	DRAWING NO C-1705536	
			RESTRICTED TO -	
			SCALE 6:1	
			SHEET 2 OF 3	
			REV B	

4

3

2

1


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
H	-	SEE SHEET 1	-	-	-	



NOTE
EMBOSS TAPE AND REEL ACCORDING EIA STANDARD 418-B

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN P. WILLEMS 19-04-04	 TYCO ELECTRONICS NEDERLAND B.V. 's-HERTOGENBOSCH, THE NETHERLANDS	
		CHK P. JAEGER 19-04-04		
		APVD P. JAEGER 19-04-04	NAME -	
DIMENSIONS: mm		PRODUCT SPEC 108-19269	10 Pos Compressive Connector -	
		APPLICATION SPEC -		
		WEIGHT -	SIZE A3	CAGE CODE 00779
MATERIAL -		FINISH -	DRAWING NO C=1705536	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 6:1	SHEET 3 OF 3
			REV B	