



NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\phi .139$ MAX ON $1.000 \pm .002$ CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS		ELECTRICAL DATA		SCALE		DO NOT SCALE PRINT	
OPERATING FORCE----- 2 OZ MAX		CONTACT ARRANGEMENT		FULL		SCALE PRINT	
RELEASE FORCE----- 1/4 OZ MIN		S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		ONE PLACE (.0)	
DIFFERENTIAL TRAVEL----- .001 - .006		L103		TWO PLACE (.00)		THREE PLACE (.000)	
OVERTRAVEL----- .094 MIN		15A 125, 250 OR 480 VAC 1/8HP 125 VAC, 1/4HP 250 VAC		ANGLES		±	
				WEIGHT		.076 LB	
		L288 L306 L315					

REVISONS	CHECK	DATE
A	0001190	19 JAN 06
JUH	20 AUG 03	
B	0018004	19 JAN 06
TSG		

RJ	CHECK	30 MAY 03
SAV	CHECK	30 MAY 03