






LOC	DIST	REVISIONS ÄNDERUNGEN					
		P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
A1	-	PROJEKT NR.:					
			E1	CUT OFF ADDED BY AREA LEAD-IN CHAMFER	31MAY2012	KHH	HEIN
			F1	LOCKING LATCHES OF FEMALE SHELL CHANGED	02OCT2013	SH	DO
			F2	TITLE BLOCK: NAME CHANGED	09OCT2015	ER	DO



PN 0-1 AS SHOWN




PN 0-2 AS SHOWN



- Notes
- 1 SUITABLE POWER INSERT: SERIES HC26
CUSTOMER DRAWING: 1103429
 - 2 SUITABLE CAT5e CABLE:
CUSTOMER DRAWING: 1103536
 - 3 SUITABLE CRIMP CONTACTS:
CUSTOMER DRAWING: 1658686
 - 4 SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 91285
 - 5 SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 91285
 - 6 STANDARDS:
DIN EN 61984, DIN EN 60664-1
 - 7 POLARIZATION RIP
 - 8 FOR WIRE-SHIELDING DIAMETER 5.0
 - 9 FOR WIRE-SHIELDING DIAMETER 4.2
 - 10 PACKAGING:
40 SETS IN A CARTON, UNMOUNTED

1	-	FERRULE	BRASS	SILVER PLATED	SERIES HC26, FEM. SHELL CRIMP VERSION	8	4
-	1	FERRULE	BRASS	SILVER PLATED	SERIES HC26, FEM. SHELL STANDARD	9	3
1	1	FEMALE SHELL	COPPER ALLOY	SILVER PLATED	SERIES HC26, 4 POS. 22 DF		2
1	1	FEMALE INSERT ASS'Y	PBT-GF10	GREY	SERIES HC26, 4 POS. 22 DF		1
0-2	0-1	DESCRIPTION	MATERIAL	COLOR/SURFACE	NOTE		ITEM
PN/QTY							

PARTS LIST (PER ONE UNIT)

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).				TOLERANCING ISO 8015 TOLERIERUNG ISO 8015																	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).				DWN H.BRAUN 19OCT2007		 TE Connectivity															
				CHK T.VETTER 27OCT2008																	
				APVD T.SCHNURPFEIL 27OCT2008																	
DIMENSIONS: MASSEINHEITEN: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES/WINKEL ±-		NAME		FEMALE INSERT ASS'Y SERIES HC26, 4-POS., 22DF CIRCULAR HYBRID CONNECTOR															
				PRODUCT SPEC PRODUKTSPEZ. 108-74097																	
				APPLICATION SPEC VERARBEITUNGSSPEZ. 114-74103																	
				SIZE						CAGE CODE		DRAWING NO ZEICHNUNGS-NR.		RESTRICTED TO NUR FUER							
				MATERIAL -						FINISH/OBERFLAECHE/FARBE -		A3		00779		C=1103427		-			
CUSTOMER DRAWING				/KUNDENZEICHNUNG				SCALE MASSSTAB		2:1		SHEET BLATT		1		OF VON		1		REV F2	