



MARKING:



MARKING:



WIRING COLOR:

E: Yellow/Green

N: Blue

L: Brown

LENGED ON CORD: (204-14)

VDE KEMA-KEUR ANS NIE NIE VDE CEBEC 809

NF-USE 1346 IEMMEQU H05VV-F 3G 0.75mm² 60227 IEC 53 RVV 300/500V

A003083 3ASL/75 4V-75 V-75(75°C) 250/440V ORDINARY DUTY Q88228 -LF- CE

No	BOM ITEM	Q'TY	P/N
1	SAA-118 BLADE	1 pcs	BBN11800
2	SAA-118 INSULATION BLADE	2 pcs	BBN1181N
3	SP-502B INNER BODY	1 pcs	M1502000
4	PVC 45P (SA87, SP-502B)	40 g	RPP04512
5	∅2.35B PHOSPHOR BRONZE TUBE	2 pcs	BPP235B3
6	∅3.2 PHOSPHOR BRONZE TUBE	1 pcs	BPP32300
7	IS-034 INNER BODY	1 pcs	MP334012
8	PVC 45P (SA87, IS-034)	15 g	RPP04512
9	PE TIE (BLACK, 6 inch)	1 pcs	KBB10006

CABLE	H05VV-F 3G 0.75 DENT PRINT CT-12 (BLACK)				
PLUG	SP-502B + IS-034	LENGTH	2000	UNIT	mm
NAME		N/W		UNIT	kg
P/N	P-AUSC5B2	SG DWG	SR-140085-3	VER.	A

V5I 6B3016 12 200 00