


VOLEX RESERVES THE RIGHT TO ALTER NON-CRITICAL DIMENSIONS WITHOUT NOTICE.

PACKAGING: FOLD & TIE



V

CUD

FORM IN71-07 REV.A

<input checked="" type="checkbox"/> Indianapolis, IN <input type="checkbox"/> Conover, N.C. <input type="checkbox"/> Freemont, CA <input type="checkbox"/> Aguascalientes, MX <input type="checkbox"/> Tijuana, Mexico <input type="checkbox"/> Hermosillo, MX <input type="checkbox"/> Clinton, AR <input type="checkbox"/> Kanata, Canada	<p><b>Proprietary Notice:</b></p> <p>This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.</p>
--	---

<p><b>MATERIAL:</b> PLUG: PVC-BLACK JACKET: PVC-BLACK ROHS Compliant</p>	<p><b>FINISH:</b> JACKET: SMOOTH</p>
--	--

REV	SCALE	ECD:	ITEM DESCRIPTION	DESCRIPTION	DATE
1	NDT TO SCALE	N/A	C.U.D - NEW RELEASE		06/03/04
2			FORMAT UPDATE		08/18/04
3			REVISED DRAWING TO SHOW ROUND PINS CLR		11/13/06

**NOTES:**

- 1) CORDAGE: HD5VVF3G 1.00 sq.mm/BLACK
- 2) APPROVALS:
- 3) RATING: 10 AMP/250 VOLTS
- 4) CORDAGE O.D. : .272 (REF.)
- 5) PACKAGING: 40 PIECES/CARTON
- 6) ALL DIMENSIONS IN inches.

<p><b>TOLERANCE UNLESS OTHERWISE SPECIFIED</b></p> <p>.XXX ± .005 .XX ± .02 .X ± .03 FRACT. ± 1/32° ANGULAR ± 1/2°</p>	<p><b>APPROVED</b></p> <p>CR</p>	<p><b>DRAWN BY</b></p> <p>ARK</p>	<p><b>DATE:</b></p> <p>06/03/04</p>
--	----------------------------------	-----------------------------------	-------------------------------------

PART NO. 2115H 10 C3