






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	39	P2		REVISED PER ECO-11-010839	25MAY11	RK	HMR



- ① PBT
- ② LCP
- ③ TOLERANCE IS $+.007/-0.003$ FOR 6 POSITION AND SMALLER SIZES.



DETAIL FOR -1 ONLY
(2 POSITION)

DETAIL FOR -2 ONLY
(3 POSITION)

②	2.595	2.520	2.400	24	25	2-103653-4
②	2.495	2.420	2.300	23	24	2-103653-3
②	2.395	2.320	2.200	22	23	2-103653-2
②	2.295	2.220	2.100	21	22	2-103653-1
②	2.195	2.120	2.000	20	21	2-103653-0
②	2.095	2.020	1.900	19	20	1-103653-9
②	1.995	1.920	1.800	18	19	1-103653-8
②	1.895	1.820	1.700	17	18	1-103653-7
②	1.795	1.720	1.600	16	17	1-103653-6
②	1.695	1.620	1.500	15	16	1-103653-5
②	1.595	1.520	1.400	14	15	1-103653-4
②	1.495	1.420	1.300	13	14	1-103653-3
②	1.395	1.320	1.200	12	13	1-103653-2
②	1.295	1.220	1.100	11	12	1-103653-1
②	1.195	1.120	1.000	10	11	1-103653-0
②	1.095	1.020	.900	9	10	103653-9
②	.995	.920	.800	8	9	103653-8
②	.895	.820	.700	7	8	103653-7
②	.795	.720	.600	6	7	103653-6
①	.695	.620	.500	5	6	103653-5
①	.595	.520	.400	4	5	103653-4
①	.495	.420	.300	3	4	103653-3
①	.395	.320	.200	2	3	103653-2
①	.295	.220	.100	1	2	103653-1
MATERIAL	D	C	B	A	NO OF POSN	PART NUMBER
COLOR-BLACK						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 28JUL00				
DIMENSIONS: INCHES		CHK K WRIGHT 28JUL00				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K WRIGHT 28JUL00	NAME			
0 PLC ± -		PRODUCT SPEC	PIN HOUSING, AMPMODU			
1 PLC ± -		APPLICATION SPEC	MTE, SINGLE ROW, .100 CL			
2 PLC ± -		108-25034	POLARIZED WITH LATCH			
3 PLC ± .005		114-25026	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -		WEIGHT	A2	00779	C=103653	-
ANGLES ± -		FINISH	SCALE 4:1			SHEET 1 of 1
FINISH		CUSTOMER DRAWING	REV P2			