



M-5435 2



NOTES:

1. WIRE CAPACITY: #8AWG TO #4AWG COPPER WIRE ONLY.
2. CORD RANGE: Ø.83 TO 1.30, TYPE "S" OR "SO".  
[21.1] [33.0]
3. ALL DIMS. TO BE INCHES.  
[mm]

CODE 74545

TITLE  
50A 250VAC, 2 POLE, 3 WIRE  
MOBILE X-RAY HUBBELLOCK CAP  
GROUNDED

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
INSULATOR	DUREZ	BLACK
CONTACTS	BRASS	
CLAMPS	ALUMINUM	1-GREEN
CLAMP SCREWS	STEEL	ZINC PL.
GR. SHUNT	Ø31 BRASS	
CENTER POST	STEEL	ZINC PL.
COVER	Ø62 STEEL	WHITE
RETAINER COVER	LEXAN	GRAY
BUSHING	RUBBER	
EPOXY KIT	(NOT SHOWN)	
REDUCERS	RUBBER	

SYM	REVISIONS	APP	DATE
1	SPEC'S. REVISED	JPP	9-18-73
2	ADDED NOTES 1 TO 3; REMOVED "RUBBER GRIP" CALLOUT; "HBL25515" WAS "25515"; ADDED "NOT SHOWN" TO "EPOXY KIT" IN PARTS LIST; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	2/5/05

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
FRACTIONS ± 1/64		BRIDGEPORT, CONN.	
DECIMALS ± .005		DR BY <u>ASM</u>	APP BY _____
ANGLES ± 2°		TR. BY _____	SCALE <u>1E1</u>
		CHK'D. BY _____	DATE <u>2-9-72</u>

DIMENSION SHEET FOR CAT. NO. HBL25515

REPAIRABLE  NON-REPAIRABLE

B

M-5435

2