








24.6	24.62	23.6	25.55	55339-1207	120
18.6	18.62	17.6	19.55	55339-0907	90
16.6	16.62	15.6	17.55	55339-0807	80
12.6	12.62	11.6	13.55	55339-0607	60
D	C	B	A	MATERIAL NO.	CIRCUIT

MODEL NO.	55339-***7
-----------	------------

MODEL NO. 55555 ***		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
---------------------	--	----------------------------	--	--------------	------------------------	---------------------------


DRAWN BY	DATE	TITLE	REVISION	PROJECTION
M.HAYASHI	1998/08/28	0.4 MM B-TO-B CONN PLUG ASSY (HGT=4MM)		
CHECKED BY	DATE			
T. ITO	2000/10/23			

APPROVED BY M.FUKUSHIMA	DATE 2000/10/23	 MOLEX INCORPORATED
----------------------------	--------------------	--




MATERIAL NO.	DOCUMENT NO.	SHEET NO.
SFF CHART	SD-55339-003	1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

REVISED	EC NO: J2005-3657	2005/08/19	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	DRW:K.SASAKI	2005/08/19		10 UNDER	± 0.2
	CHKD:THIRATA	2005/08/19		10 OVER 30 UNDER	± 0.25
	APPR:THIRATA	2005/08/19		30 OVER	± 0.3
				ANGULAR	± 3 °
			REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	




引き出し方向
PULL OUT
DIRECTION




DETAIL "F"

NOTES

- 製品詳細寸法については図面 SD-55339-003 を参照下さい。
RE DETAILED DIMENSION, SEE SD-55339-003
- 梱包数量：1500個/リール
NUMBER OF CONNECTORS：1500PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- トップテープの剥離強度：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.



- 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE)：PET, PE, PEF
リール(REEL)：ポリスチレン(P.S) <リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>

MODEL NO. 55339-***8

REVISED EC NO: J2008-3743 DRAWN: KINOSHITA CHKD: T. HARUYAMA APPR: NUKITA	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
				MM ONLY		---	METRIC			
		10 UNDER	± 0.2	DRAWN BY	DATE	TITLE 0.4 BTB CONN PLUG ASSY HGT=4 EMBSTP PKG				
		10 OVER 30 UNDER	± 0.25	M. HAYASHI	1998/08/28					
		30 OVER	± 0.3	CHECKED BY	DATE					
		T. ITO	2001/02/21							
		APPROVED BY	DATE							
M. FUKUSHIMA	2001/02/21									
ANGULAR		± 3 °	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-55339-004		1 OF 3				
D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F

E


D

C

B



A

引き出し方向
PULL OUT
DIRECTION



SECT:Y-Y

32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE



SECT:X-X
(SCALE:4-1)

32	33.5	17.75	55339-0808	80
		13.75	55339-0608	60
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 CKT.
MODEL NO.	55339-***8			

REVISED EC NO: J2008-3743 DRWN:K INOSHITA 2008/05/12 CHKD:T HARUYAMA 2008/05/13 APPR:NUKITA 2008/06/26 REV D	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
				MM ONLY		---	METRIC		
		10 UNDER	± 0.2	DRAWN BY M.HAYASHI	DATE 1998/08/28	TITLE 0.4 BTB CONN PLUG ASSY HGT=4 EMBSTP PKG			
		10 OVER 30 UNDER	± 0.25	CHECKED BY T. ITO	DATE 2001/02/21				
		30 OVER	± 0.3	APPROVED BY M.FUKUSHIMA	DATE 2001/02/21	MOLEX INCORPORATED			
	ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.				
REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE		SD-55339-004				2 OF 3	
		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C

B

A



44	45.5	25.75	55339-1208	120
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 CKT.

MODEL NO.	55339-***8
-----------	------------

REVISED EC NO: J2008-3743 DRWN:K INOSHITA 2008/05/12 CHKD:T HARUYAMA 2008/05/13 APPR:NUKITA 2008/06/26 D	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
				MM ONLY		---	METRIC		
		10 UNDER	± 0.2	DRAWN BY	DATE	TITLE 0.4 BTB CONN PLUG ASSY HGT=4 EMBSTP PKG			
		10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE				
		30 OVER	± 0.3	APPROVED BY	DATE	MOLEX INCORPORATED			
	ANGULAR ± 3 °		M.FUKUSHIMA	2001/02/21	MOLEX				
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.					DOCUMENT NO.	
SEE TABLE			SD-55339-004		3 OF 3				
REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				