


DRAWING No.
152188

SHT. 1
OF
1 SHTS.

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY HELLERMANN TYTON. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF HELLERMANN TYTON.

THIRD ANGLE PROJECTION




BS 8888



DO NOT SCALE
IF IN DOUBT ASK

Q.A.	H/S SETT
H/S Q.A.	REL. INSP.
H/S PROD	EXT. ISS. CODE 7

STANDARD PART (AFTER UNRESTRICTED RECOVERY)



EXPANDED (AS SUPPLIED)



PART No.	EXPANDED DIAMETERS (AS SUPPLIED)		RECOVERED DIAMETERS		RECOVERED DIMENSIONS						
	ϕh	ϕj	ϕH	ϕJ	P	R	S	T	V	Hw	Jw
	MIN	MIN	MAX	MAX	$\pm 10\%$	NOM	NOM	$\pm 20\%$	MAX	$\pm 20\%$	$\pm 20\%$
120-41	16.5 (0.65)	10.7 (0.42)	7.0 (0.28)	3.0 (0.12)	38.0 (1.50)	24.0 (0.94)	9.10 (0.36)	1.0 (.04)	3.0 (0.12)	1.30 (0.05)	1.30 (0.05)
120-42	16.5 (0.65)	10.2 (0.40)	7.0 (0.28)	3.0 (0.12)	60.9 (2.40)	24.0 (0.94)	32.0 (1.26)	1.0 (.04)	3.0 (0.12)	1.30 (0.05)	1.30 (0.05)
120-43	24.0 (0.94)	16.0 (0.63)	7.0 (0.28)	3.0 (0.12)	38.0 (1.50)	24.0 (0.94)	9.10 (0.36)	1.0 (.04)	3.0 (0.12)	1.30 (0.05)	1.30 (0.05)
120-51	14.0 (0.55)	6.0 (0.24)	7.0 (0.28)	3.0 (0.12)	38.0 (1.50)	24.0 (0.94)	9.10 (0.36)	1.0 (.04)	3.0 (0.12)	1.30 (0.05)	1.30 (0.05)

HellermannTyton

William Prance Road,
Plymouth International Med. & Tech. Park,
Plymouth, PL6 5WR
Tel ++44 (0) 1752 701261
Fax ++44 (0) 1752 790058

NAME	G.Baser	SCALE	NTS	ADHESIVE	A3 ORIGINAL SHEET SIZE 420mm x 297mm	SHT. 1 OF 1 SHTS.
DATE	19/02/09	DIMS IN	mm (in)			
TITLE	BOTTLE SLEEVE (RIBBED)			PART No.	120	DRAWING No.
					152188	

2	P1329	G.B.	11/10/10
1	P1260	G.B.	19/02/09
ISSUE	NOTE No.	DRAWN	DATE