




ALTW
CONFIDENTIAL
2016-07-13
R&D DEPT.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313C0042	2013/11/25	Tom_gu	Change Tolerance And Length
C	LEN1570126~8	2015/06/24	Jason.Yu	Add Conn.2 Pin Out & LOGO
D	LEN1670201~203	2016/07/13	Jinhai	Change Supplier



USB3.0 Half Finished



Shield	Braid	編織	Shield	
9	Orange	28AWG	橙	9
8	Purple	28AWG	紫	8
7	Drain	28AWG	地線	7
6	Yellow	28AWG	黃	6
5	Blue	28AWG	藍	5
	Drain	28AWG	地線	
4	Black	28AWG	黑	4
3	Green	28AWG	綠	3
2	White	28AWG	白	2
1	Red	28AWG	紅	1
Conn.1	Wire Color		Conn.2	
	Pin Out			

Note:
 * Ⓞ Important Dimension.
 * Housing: ABS, Black
 * Screw Nut: Nylon+GF, Black
 * Gasket: Silicone, Gray
 * Jack: USB3.0-A Female Solder
 * Cable: UL2725 (1P*28#+DMA)*2C+1P*28#+2C*28#+ADB, PVC, UV Resistant, OD=6.0mm, Black
 * Cable Length Tolerance: 150~300mm:±15mm
 * Use with waterproof cap or dust cap
 * Use without waterproof cap or dust cap
 * All of Drain twisted together.

Waterproof Rate: IP67
 UA-30PMF-SD7BXX
 △ XX : 150~300mm
 15 : 150mm
 20 : 200mm
 30 : 300mm
 Cable Length(L): 150~300mm

UNIT:mm
 TOLERANCE
 ±0.5

TITLE USB3.0 Male A Type			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. B.3	Ⓞ: Inspection item	

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY Jinhai	DATE 2016-07-13
DWG NO. UA-30PMF-SD7BXX	CHECKED BY Feng-Li	DATE 2016-07-13
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2016-07-13

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.