



	P1		P2		P1		P2
BLUE	1	—————	1	BLUE	11	—————	11
BLUE	2	—————	2	BLUE	12	—————	12
GREEN	3	—————	3	GREEN	13	—————	13
GREEN	4	—————	4	GREEN	14	—————	14
BLACK	5	—————	5	BLACK	15	—————	15
BLACK	6	—————	6	BLACK	16	—————	16
WHITE	7	—————	7	WHITE	17	—————	17
WHITE	8	—————	8	WHITE	18	—————	18
RED	9	—————	9	RED	19	—————	19
RED	10	—————	10	RED	20	—————	20

3	UL1061 18AWG, LENGTH (L+7mm), BLUE(4pcs),GREEN(4pcs),BLACK(4pcs),WHITE(4pcs),RED(4pcs)	20	M304
2	WAFER: CKM4201WV-20P	1	M31
1	TERMINAL: CKM4201-T MALE	20	M31
	HOUSING: CKM4201-20P MALE	1	M31
No.	DESCRIPTION	Q'TY	Supplier

APPROVED			Cable Length Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED			
DRAWING		ITEM NO. <b>RB-526</b>	