





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	PART DESCRIPTION	PRINT-ON HEIGHT "A" inches [mm] +/- .031	WIDTH inches [mm]	LENGTH inches [mm]	MIN. CABLE O.D. inches [mm]	MAX. CABLE O.D. inches [mm]	STD. PKG. CARDS	STD. CTN. CARDS
S100X125VARY	GMV3	(1) DISPENSER (1) ROLL, WHITE WRITE-ON VINYL LABEL, 200/ROLL (1) PFX-0	0.375 [9.52]	1.00 [25.4]	1.25 [31.75]	0.12 [3.07]	0.28 [7.03]	1	10
S100X125VAFY		REFILL ROLLS: WHITE WRITE-ON, VINYL LABEL, 200/ ROLL							
S100X225VARY	GMV3	(1) DISPENSER (1) ROLL, WHITE WRITE-ON VINYL LABEL, 100/ROLL (1) PFX-0	0.75 [19.05]	1.00 [25.4]	2.25 [57.15]	0.24 [6.06]	0.48 [12.13]	1	10
S100X225VAFY		REFILL ROLLS: WHITE WRITE-ON, VINYL LABEL, 100/ ROLL							

NOTES:

1. DIMENSION IN [] ARE IN MILLIMETERS.



CAD FILENAME/LAYERS 100397HN-DC-C10562/05B

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
SELF-LAM. WIRE MARKER
S100X***VARY AND S100X***VAFY

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .015
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	3/30/11	RVU		ADD NEW ISO VIEW. UPDATE TABLE. REVISE TOLERANCES.	4855	R		
0	1-25-07	RVU		DRAWING RELEASE.	4855	R		

DRAWN BY RVU	MAT'L:	SCALE NTS
DATE 1-25-07	SEE TABLE	DRAWING NO. C10562
CHK'D		DWG A SIZE