



Dimension	Linear dimension tolerance					Roundness and chamfer			Angle
	With 1/3	Over 1/3 to 1	Over 1 to 3	Over 3 to 10	Over 10	With 1/3	Over 1/3 to 1	Over 1	
Tolerance	±0.1	±0.1	±0.2	±0.3	±0.5	±0.2	±0.5	±1	±1°
	±0.2	±0.3	±0.5	±0.8	±1.2	±0.4	±1	±2	±3°

SPECIFICATIONS

VOLTAGE RATINGS: 300V
 CURRENT RATINGS: 50A
 CONDUCTORS: ALUMINUM
 MATERIALS: PF UL94V-0
 SUITABLE WIRE:
 LINE: 2~14 AWG CU
 LOAD: #250

WIRING TORQUE:
 LINE:
 2~3 AWG 50 LB-IN
 4~6 AWG 45 LB-IN
 8 AWG 40 LB-IN
 10~14 AWG 35 LB-IN
 LOAD:
 #250

CERTIFICATION MARKING: CQC UL CUL

5	RIVET	COPPER ; 7/16-20UNF	6	Sn ²⁺ PLATED	R11
4	SCREW	SS ; 5/16-24UNF	3	Sn ²⁺ PLATED	SC311Y
3	METAL FITTING	BRASS ; 10.8 #250	3	Ni PLATED	PR1-2
2	CONDUCTORS	ALUMINUM AL6061	3	Sn PLATED	AL-1
1	BASE	PF ; UL94V-0	1		JBW101-1-3P BLACK

NO.	DATE	CONTENT	REVISER	APPROVED	NO.	PART NAME	MATERIAL	Q'TY	FINISH	PART NO.	REMARK
SCALE		1/1	DIM. mm		DRAWN BY		CHECKED BY	APPROVED BY	TITLE		
HOPPY INDUSTRIAL CO.,LTD.					L.F.	L.W.S.	L.W.S.		TERMINAL BLOCK		
					16.08.29	16.08.29	16.08.29		DWG NO.		HP-AT101-1-3P (HO)