


Electrical Test:

1. 100% Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 5M ohm min.
4. Hi-pot: 300V DC/10ms

Pin Assignment



NO	DESCRIPTION	QTY	UNIT	TOLERANCE			TITLE:	CUSTOMER :	CUSTOMER P/N :	SCALE	NONE	DRAWING NO.:	REV.
				INCHES	M/M								
6	Metal DOWN Cap	1	pcs	.X	.015	.30	USB2.0 Type Cable C TO C BLACK L=0.5M	CPC	PSG91484	NONE	MM	C06026-00267	A01
5	Metal UP Cap	1	pcs	.XX	.010	.10							
4	45P Color:White PVC	12	g	.XXX	.005	.05							
3	Inside Molding:Polyamide Resin	1	g	DRAWN BY 邱建联			CUSTOMER P/N :						
2	TYPEC-USB2.0 C Type Connector With PCB,Insulation:White,Shell Nickel Plated	2	pcs	CHECK BY			DATE	2017.05.02					
1	NO UL 30AWG(19/0.06TC)*1P+22#(41/0.10TC+250D)*1C+30AWG(7/0.10TC)*1C+3E(26/0.10+250D)+AB(16/9/0.06TC 85%) OD:3.6 PVC White No Marking	AR	m	APPD BY									
NO	DESCRIPTION		UNIT				DATE	2017.05.02					1/2