

4

3


2

1


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		I	FIRST ISSUE	02JAN01	RC	JJ
			A	EBD0-0334-04	29SEP2004	RS	NC

ITEM NO	DESCRIPTION	QTY/ ASSY
1	16-14 R/T BODY SOLIS - 5/16" STUD	2
2	BRAIDED CABLE - 2.26mm ²	A/R
3	HEATSHRINK RNF-100 BLACK	A/R



200 ±5	1337710-3
150 ±5	1337710-2
100 ±5	1337710-1
DIM 'A'	TYCO PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R.CHURCHILL 02JAN2001		tyco Electronics AMP of Great Britain Ltd., Stanmore, Middlesex, HA7 4RS.		
		CHK D.CHICK 02JAN2001				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2.26mm CSA BRAID M8-M8		
		APVD J. JEWELL 02JAN2001				
		PRODUCT SPEC -				
		APPLICATION SPEC -				
		WEIGHT -				
		MATERIAL -		FINISH -		
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV A