




DO NOT SCALE DRAWING

本図は2列品を示す
DUAL ROW ASS'Y



- 注記
NOTES
- 1. 適合ターミナル : 56265/56279シリーズ
APPLICABLE TERMINAL : 56265/56279 SERIES
 - 2. 適合ターミナル : 56187/56188シリーズ
APPLICABLE TERMINAL : 56187/56188 SERIES
 - 3. 適合リテーナー : 51348-***1* シリーズ
APPLICABLE RETAINER : 51348-***1* SERIES
4. 材料
MATERIAL : NYLON66, UL94V-0

51347-1200	51348-0613	NATURAL	16.5	21.7	12	51346-1200	
-1000	-0513		13.2	18.4	10	-1000	51346-****
-0800	-0413		9.9	15.1	8	-0800	
-0600	-0313		6.6	11.8	6	-0600	
51347-0420	51348-0213	NATURAL	3.3	8.5	4	51346-0420	
MATE WITH	CONFORMABLE-RETAINER	COLOR	B	A	CKT.	MATERIAL NO.	MODEL NO.

1684NO. DRWN: CHK: APPR:		1683NO. DRWN: CHK: APPR:		1682NO. DRWN: CHK: APPR:		1681NO. DRWN: CHK: APPR:		RELEASED 1680NO. J2004-1974 DRWN: T.ODA '04/01/19 CHK: S.ICHIKAWA APPR: YO.IITO		DESCRIPTION		MATERIAL 材料		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE —#—		DESIGN UNITS ☒ mm ☐ INCH		 THIRD ANGLE PROJECTION		☐ mm INCH ☐ mm INCH ☒ mm ONLY		REVISE ON CAD ONLY	
												—//—		10 UNDER 未満		±0.2		DRAWN BY & DATE TODA '04/01/15		TITLE: 3.3 mm WIRE TO WIRE CONN. PLUG HOUSING					
												FINISH 仕上付		10 OVER 以上 30 UNDER 未満		±0.25		CHECKED BY & DATE S. Ichikawa.							
												WIRE RANGE 適用電線範囲		30 OVER 以上		±0.3		APPROVED BY & DATE Y.Ito		MOLEX INCORPORATED					
												—//—		ANGLE 角度		±3°		CAD FILENAME SD-51347-001.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-51346-001		SHEET NO. 1 OF 2	
														1685 DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				SIZE B							

