





contact face acc. to  
IEC 61076-2-101



|                         |                                             |
|-------------------------|---------------------------------------------|
| conductor cross section | 0.14 - 0.34mm <sup>2</sup><br>AWG26 - AWG22 |
| cable outside diameter  | 4.0 - 5.1mm                                 |

|                                                                                                                                                                         |                                               |                                              |                                                          |                                    |                         |                             |                                                         |                        |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|----------------------------------------------|----------------------------------------------------------|------------------------------------|-------------------------|-----------------------------|---------------------------------------------------------|------------------------|
|   |                                               | All Dimensions in mm<br>Original Size DIN A4 |                                                          | Scale<br>2:1                       | Free size tol.          |                             | Ref.<br>Sub. TB 21011323081 / 500000060894 / 17.04.2013 |                        |
|                                                                                      | All rights reserved                           |                                              |                                                          | Created by<br>HELLMANN             | Inspected by<br>EISFELD | Standardisation<br>HOFFMANN | Date<br>2016-05-30                                      | State<br>Final Release |
|                                                                                                                                                                         | Department EC PD - DE                         |                                              |                                                          | Title<br>HARTING M12-S male 3-pole |                         |                             |                                                         |                        |
|                                                                                                                                                                         | HARTING Electronics GmbH<br>D-32339 Espelkamp |                                              |                                                          |                                    |                         |                             |                                                         |                        |
|                                                                                                                                                                         |                                               |                                              | Type<br>TB                                               | Number<br>21011323081              |                         |                             | Rev.<br>B                                               | Page<br>1/1            |
|                                                                                                                                                                         |                                               |                                              | Doc-Key / ECM-Nr.<br>100190975/UGD/005/B<br>500000103382 |                                    |                         |                             |                                                         |                        |