



Datenblatt - Fiche technique - Data sheet

11.02.8870



ROLINE USB 3.0 Kabel, Typ A-B, 1,8m

ROLINE Câble USB 3.0 Type A-B, 1.8m

ROLINE USB 3.0 Cable, A - B, M/M, 1.8 m






ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△	B	ECR # 090616-6 ADD BAR CODE NO.	06/16/09'

USB 3.0 A/M 9PIN
INS:BLUE(P/T 300C)

L+T

USB 3.0 B/M 9PIN
INS:BLACK



NOTE:

- 1.CABLE: UL-2725 [#28(7/0.127 T.C)×1P INS:Foam-PE+D.W(7/0.127 T.C)+AL/MY +Hot-melt-Mylar]×2C+#28(7/0.127 T.C)×1P INS:Polyolefin +#28(7/0.127 T.C)×2C INS:Polyolefin + AL/MY + B.D(85%) PVC JACKET; OD:5.2±0.15mm COLOR:BLACK(NK-K01) REV 3.0.
- 2.CONNECTOR:
 - P1: USB 3.0 A TYPE MALE 9PIN CONTACT:30U",SHELL:NI-PLATED.
 - P2: USB 3.0 B TYPE MALE 9PIN CONTACT:30U",SHELL:NI-PLATED.
- 3.HOOD:MOLDED TYPE,PVC 45P, COLOR:BLACK(NK-K01).
- 4.ELECTRICAL TEST:

PIN OUT			
P1		P2	
1	RED	1	PWR
2	WHITE	2	UTP_D-
3	GREEN	3	UTP_D+
4	BLACK	4	GND_PWRrt
5	BLUE	5	SDP1-
6	YELLOW	6	SDP1+
7	D.W	7	SDP1_Drain & SDP2_Drain
8	PURPLE	8	SDP2-
9	ORANGE	9	SDP2+
	SHELL	9	SHELL

- (1)100% OPEN SHORT & MIS WIRE TEST.
- (2)CONTACT RESISTANCE 3 ohm Max.
- (3)INSULATION RESISTANCE 10M ohm Min.
- (4)HI-POT DC300V
- 5.PACKING: EACH PC / POLYBAG + HEADER CARD + BAR CODE LABEL.



DWG	P/N	L(mm)	T(mm)	HEADER CARD	PCS/CARTON	BAR CODE NO.
170-3591-2	11.02.8871	3000	30	BIG HEADER CARD	50	7611990188307
170-3591-1	11.02.8870	1800	30	SMALL HEADER CARD	50	7611990188291

Tolerance Inch M/M		Title USB 3.0 A/M - B/M CABLE
X	.015 .30	
.XX	.010 .10	
.XXX	.005 .05	
Draw FANNIE 06/16/09'		Customer P/N
Check		App'd
Engr		Scale NONE
		Units M/M
		Third Angle Projection
		Dwg No. 170-3591
		REV: B
		Sheet: 1/1

Rotronic co., LTD.