


M-8931

2



NOTES:

1. DIMENSIONS ARE INCHES $\pm .02$
[mm] $\pm .5$
2. RATING: 600VAC/250VDC 400 AMP
3. UL/c-UL ENCLOSURE TYPES 3R, 4X, 12,
SEE INSTRUCTION SHEET

CODE 74545

HUBBELL CAT. NO.	COLOR
HBLPTBK	BLACK
HBLPTW	WHITE
HBLPTGN	GREEN
HBLPTBR	RED
HBLPTBL	BLUE
HBLPTO	ORANGE
HBLPTBN	BROWN
HBLPTY	YELLOW

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	TPE	SEE TABLE
FEMALE CONTACT	BRASS	
RIVET	BRASS	
MALE CONTACT	BRASS	

2	REMOVE $\phi 1.06$ [27.0] & $\phi 1.22$ [30.9] ADD $\pm .02$ & $\pm .5$ TO NOTE 1 CHANGED NOTE 3 PER DCN 11484 TwB	12/15/04
1	RELEASED PER DCN 10992 MJM TB	8/25/03
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE SINGLE POLE
PARALLING TEE
FEMALE/MALE/MALE

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT
FRACTIONS $\pm 1/64$	DR. BY MJM APP. BY
DECIMALS $\pm .005$	TR. BY SCALE 1:1
ANGLES $\pm 2^\circ$	CHK'D BY DATE 6/11/03

DIMENSION SHEET FOR CAT. NO.
SEE TABLEREPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-8931

2