




DESCRIPTION: M5 FEMALE - RIGHT ANGLE - PANEL MOUNT - 2 POSITION


UNITS = INCHES [MM]



NUT





P.C.B LAYOUT



PANEL CUT-OUT

853-002-213R00Y

1 = GOLD FLASH
4 = 10u" GOLD



NOTE:

MATERIAL

HOUSING:

CONTACT:

NUT:

O-RING:

BACK HOUSING

DOWN HOUSING

PBT UL94V-0, BLACK

BRASS

BRASS

NBR, BLACK

PBT UL94V-0, BLACK

PBT UL94V-0, BLACK

FINISH

CONTACT:

NUT:

GOLD PLATED
OVER 50u" NICKEL
NICKEL PLATED

ELECTRICAL

RATED CURRENT:

RATED VOLTAGE:

INSULATION RESISTANCE:

CONTACT RESISTANCE:

WATER PROOF:

1A

60V

100 MOhms MIN.

10 MOhms MAX.

IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-03-16

CHECKED:

DATE:

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

3

DWG NO.

853-002-213R00Y