





RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲5. OPERATING FORCE: 130 ± 50 gms
6. TRAVEL: 0.25 +0.2/- 0.1mm
7. CONTACT RESISTANCE: 100 mΩ MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 50,000 CYCLES MIN.
- ▲9. SILVER CONTACTS
- ▲10. PACKAGE: BULK 1,000 PER BAG
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT

E-SWITCH®

F	20940	WHITE WAS BLACK	12/26/12	EBP
E	20818	RERELEASED AND REDRAWN	10/10/12	rc
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE TL1107BF130WQ				
SCALE	DATE	DR	DWG	REV
4:1	10/10/2012	rc	P010311	F

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED