



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING FORMAT	21MAR2017	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500

All dimensions in mm [Inch]

UL RECOGNIZED BY UNDERWRITERS LABORATORIES INC.
IN UL FILE MH61871-PGIS2 CATEGORY-SBP LABEL, PRINTER AND RIBBON

TE PN: CN9941-000

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		GOPALAKRISHNA HV				TE Connectivity					
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK 21MAR2017		D.BURGAT					
LABEL WIDTH:	±0.3 [.012]					APVD 21MAR2017		D.BURGAT					
WEB WIDTH:	±0.8 [.031]					NAME		SBP LABEL – WHITE – HORIZONTAL 95.3 x 25.4mm [3.75 x 1.00inch] —					
VERTICAL REPEAT:	±0.8 [.031]*									PRODUCT SPEC			
HORIZONTAL REPEAT:	±0.8 [.031]*									TTDS-211 REV. 8 OR GREATER			
PRINT POSITIONING:	±0.8 [.031]*									APPLICATION SPEC			
LEFT MARGIN:	±0.4 [.016]	MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
QUANTITY: *NON ACCUMULATING	—0 % +2 %	SEE TABLE		GLOSSY		0.336g		A2	00779	C=SBPH100375WE2.5	—		
CUSTOMER DRAWING						SCALE		NTS	SHEET		1 of 1	REV	B