


## 4-CONDUCTOR TERMINAL BLOCK LATERAL MARKING WITH FIXING FLANGE

260-331 TO 260-337




© 1992 - 2011 CADENAS GmbH











## 4-CONDUCTOR TERMINAL BLOCK LATERAL MARKING WITH FIXING FLANGE

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

260-331 TO 260-337

| ITEM-NO. (ITEM-NO.)                                  | 260-331    |
|--|------------|
| Cross section1 (Cross section / mm²)                 | 0.08 - 1.5 |
| Cross section2 (Cross section / AWG)                 | 28 - 16    |
| Strip length (Strip length / mm)                     | 8 - 9      |
| Measured voltage (Measured voltage / V)              | 400        |
| Measured shock voltage (Measured shock voltage / kV) | 6          |
| Pollution degree (Pollution degree)                  | 3          |
| Current intensity (Current intensity / A)            | 18         |
| Height (Height / mm)                                 | 17         |
| Width (Width / mm)                                   | 8          |
| Depth (Depth / mm)                                   | 25         |
| No. of connection Points (No. of connection Points)  | 4          |
| No. of potentials (No. of potentials)                | 1          |
| COLOR (COLOR)  | grau       |
| WEIGHT (WEIGHT / g)                                  | 2.55       |