



**2-CONDUCTOR DISCONNECT
TERMINAL BLOCK FOR TEST AND
MEASUREMENT CENTRE MARKING
WITH INTEGRATED TEST SOCKETS
285-135**

ITEM-NO. (ITEM-NO.)	285-135
Cross section1 (Cross section / mm²)	6 - 35
Cross section2 (Cross section / AWG)	8 - 2
Strip length (Strip length / mm)	25 - 26
Measured voltage (Measured voltage / V)	1000
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	125
Height (Height / mm)	63
Width (Width / mm)	16
Depth (Depth / mm)	86
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	79.872