



**1-CONDUCTOR PCB TERMINAL
STRIP 2 SOLDER PINS / POLE PIN
SPACING 5/5.08 MM / 0.2 IN WITH
PUSH BOTTONS**
235-402/331-000 TO 235-448/331-000

ITEM-NO. (ITEM-NO.)	235-404/331-000
Cross section1 (Cross section / mm²)	0.5 - 1.5
Cross section2 (Cross section / AWG)	20 - 16
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	17.5
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	4
Height (Height / mm)	15.5
Width (Width / mm)	21.5
Depth (Depth / mm)	12.5
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	4
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	3.15
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1 +0,1 mm