





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0162	2008/09/10	Shin	Add Note
C	LEN1530229	2014/12/25	Ruru	Change Logo



Pin Assignments
Front View



Recommended Panel Cut-Out



Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Gasket: EPDM, Black
- * Nut: Nylon+GF, Black
- * Liquid Glue: Clear

$\triangle B$ * Use with waterproof cap or dust cap
Panel Thickness max: 4.0mm

$\triangle B$ * Use without waterproof cap or dust cap
Panel Thickness max: 5.0mm

Connector ①
Gasket ③
Nut ②
With Liquid Glue

UNIT:mm		TITLE Mini Panel Lock 4Pin M Conn. M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO AU-04RMMS-LC7001	DRAWN BY Ruru	DATE 2014-12-25
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 2:1	SIZE A4	SHEET 1 OF 1		DWG NO AU-04RMMS-LC7001	CHECKED BY Rita	DATE 2014-12-25
REV. C		WC-REV. A.1	$\varnothing$ Inspection item			CUSTOMER ALTW	APPROVED BY Win	DATE 2014-12-25