

# MICRO SWITCH

FREEPORT ILLINOIS, U.S.A  
A DIVISION OF HONEYWELL


FED. MFG. CODE 91929

# MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING


## 914CEI-6A

50378-1A  
 DRAWN  
 1 AM 29 AUG 88  
 CHECK  
 REVISIONS  
 ISSUE  
 DRAWING NUMBER  
 M 914CEI-6A  
 REPLACES  
 PR - 16701  
 RELEASE NO.



### NOTE

- 1 - ZINC HOUSING FINISHED WITH GREY PAINT
- 2 - SIDE EXIT CABLE



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

### CHARACTERISTICS

OPERATING FORCE ----- 2.7 LB MAX  
 RELEASE FORCE ----- 1.0 LB MAX  
 DIFFERENTIAL TRAVEL ----- .004 MAX  
 OVERTRAVEL ----- .118 MIN

### ELECTRICAL DATA

CONTACT ARRANGEMENT  
SPDT

UL LISTED - HONEYWELL LTD.  
FILE E 41859  
5A-250 VAC  
1/10HP-125 OR 250 VAC



LR-15775

### SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED  
DIMENSIONS ARE IN INCHES  
**TOLERANCES ARE:**

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT