



SPECIFICATIONS:

DIN-RAIL MOUNTABLE GFIC RECEPTACLE WIRED TO WAGO SERIES 721 V0 POLARIZED CONNECTOR. MAXIMUM LOAD: 120VAC, 20A.

LINE, NEUTRAL & GROUND IDENTIFIED WITH L, N, AND G PRINTED ON THE CONNECTOR.
LOAD OUT LINE NEUTRAL & GROUND IDENTIFIED WITH LO, NO, AND G PRINTED ON THE CONNECTOR.

INTERNAL FUSING IS NOT PROVIDED.

NOTE: THESE DEVICES MUST BE MOUNTED INSIDE AN APPROVED ELECTRICAL ENCLOSURE. INSTALL AND GROUND PER APPLICABLE ELECTRICAL CODES

Copyright © WAGO Corp. all rights reserved. This document contains information that is proprietary to WAGO Corporation and is delivered to others on the express condition that neither it nor the information it contains will be used, disclosed, reproduced, stored or transmitted in whole or in part without the prior written consent of WAGO Corporation.

Custom P/N: 51015043

1	01/28/10	PRODUCT IS ROHS COMPLIANT	N/A	DY
REV.	DATE	DESCRIPTION	DCO	BY
		N120 W19129 Freistadt Road P.O. Box 1015 Germantown, WI 53022		
		File Name PR01084-11-1.dwg		
Title/ Ident No.		PROPOSAL 1084		Page 1 of 1
Scale NTS		Date Drawn 6/16/05	Drawn By GJW	App. By

File: