






TOP VIEW



SIDE VIEW



BOTTOM VIEW

SYMBOL COMMON DIMENSIONS			
DIM.	MIN.	NOR.	MAX.
A	---	---	2.92
A1	---	---	0.22
A2	2.7 REF		
D	6.4	6.5	6.6
E	9.9	10	10.1
W	0.35	0.4	0.45
L	0.35	0.4	0.45
e	1 BSC		
n	28		
D1	5.7 BSC		
E1	9 BSC		
SD	0.5 BSC		
SE	0.5 BSC		
aaa	0.1		
bbb	0.1		
ddd	0.1		

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M –2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10–0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB–FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: L286510+8



TITLE:
PACKAGE OUTLINE 28L SIP LGA
6.5x10x2.92mm

APPROVAL

PACKAGE OUTLINE NO.
21–100181

REV.
A

1
1

–DRAWING NOT TO SCALE–